

APV spreading chart SW Flex20 fb-Flex20-fb: pneumatic seeder with 8 outputs

PHC MycorGran 2.0

This spreading recommendation is based on a submitted fertilizer sample and only on its properties. We ask you to take this into account and check it with a mobile test bench!

PHC MycorGran-2.0 SW Flex20	
Seeding shaft in %	kg/min fb-Flex20-fb
2	0,09
3	0,12
4	0,14
5	0,16
6	0,18
7	0,20
8	0,22
9	0,24
10	0,27
11	0,29
12	0,31
13	0,33
14	0,35
15	0,37
16	0,40
17	0,42
18	0,44
19	0,46
20	0,48
21	0,50
22	0,52
23	0,55
24	0,57
25	0,59
26	0,61
27	0,63
28	0,65
29	0,68
30	0,70
31	0,72
32	0,74
33	0,76
34	0,78

PHC MycorGran-2.0 SW Flex20	
Seeding shaft in %	kg/min fb-Flex20-fb
35	0,80
36	0,83
37	0,85
38	0,87
39	0,89
40	0,91
41	0,93
42	0,95
43	0,98
44	1,00
45	1,02
46	1,04
47	1,06
48	1,08
49	1,11
50	1,12
51	1,14
52	1,16
53	1,19
54	1,21
55	1,23
56	1,25
57	1,27
58	1,30
59	1,32
60	1,34
61	1,36
62	1,39
63	1,41
64	1,43
65	1,45
66	1,47
67	1,50

PHC MycorGran-2.0 SW Flex20	
Seeding shaft in %	kg/min fb-Flex20-fb
68	1,52
69	1,54
70	1,56
71	1,58
72	1,61
73	1,63
74	1,65
75	1,67
76	1,69
77	1,72
78	1,74
79	1,76
80	1,78
81	1,80
82	1,83
83	1,85
84	1,87
85	1,89
86	1,91
87	1,94
88	1,96
89	1,98
90	2,00
91	2,02
92	2,05
93	2,07
94	2,09
95	2,11
96	2,13
97	2,16
98	2,18
99	2,20
100	2,48



PHC
Plant Health Cure

We Grow Soil.